

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285957

Luminaire Tested: P3AS13R70B2750DE010 E3DLP1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DLP1H_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 552.0 lumens
Efficiency: N/A
Efficacy: 28.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285957
CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1285957
 CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129485
5°	127096
10°	119860
15°	108763
20°	95138
25°	80255
30°	65706
35°	50969
40°	36497
45°	23103
50°	11531
55°	7034
60°	6052
65°	5552
70°	4937
75°	4575
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23103 cd/sqm



TEST NUMBER: P1285957

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	9.8
10°-20°	133.3	24.2
20°-30°	151.8	27.5
30°-40°	118.7	21.5
40°-50°	58.3	10.6
50°-60°	17.9	3.2
60°-70°	10.6	1.9
70°-80°	5.7	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.0	61.4
0°-40°	457.8	82.9
0°-60°	534.0	96.7
0°-90°	552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	552.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	590	
5°	577	54
15°	479	133
25°	332	152
35°	190	119
45°	74	58
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1285957
CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1H_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	590.5
2.5°	587.4
5°	577.4
7.5°	561.3
10°	538.3
12.5°	511.4
15°	479.1
17.5°	444.6
20°	407.7
22.5°	369.3
25°	331.7
27.5°	294.8
30°	259.5
32.5°	224.2
35°	190.4
37.5°	158.2
40°	127.5
42.5°	99.1
45°	74.5
47.5°	52.2
50°	33.8
52.5°	22.3
55°	18.4
57.5°	16.1
60°	13.8
62.5°	12.3
65°	10.7
67.5°	9.2
70°	7.7
72.5°	6.1
75°	5.4
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)