

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285963

Luminaire Tested: P3AS13R70B2750DE010 E3DLP1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DLP1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 544.1 lumens
Efficiency: N/A
Efficacy: 28.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285963

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285963

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77		
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61		
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127599
5°	125247
10°	118123
15°	107197
20°	93761
25°	79093
30°	64769
35°	50246
40°	35953
45°	22762
50°	11360
55°	6958
60°	5964
65°	5500
70°	4873
75°	4490
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22762 cd/sqm

TEST NUMBER: P1285963

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	9.8
10°-20°	131.4	24.1
20°-30°	149.6	27.5
30°-40°	117.0	21.5
40°-50°	57.5	10.6
50°-60°	17.7	3.2
60°-70°	10.5	1.9
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.1	61.4
0°-40°	451.2	82.9
0°-60°	526.3	96.7
0°-90°	544.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	582	
5°	569	53
15°	472	131
25°	327	150
35°	188	117
45°	73	57
55°	18	18
65°	11	10
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1285963

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	581.9
2.5°	578.9
5°	569.0
7.5°	553.2
10°	530.5
12.5°	504.0
15°	472.2
17.5°	438.1
20°	401.8
22.5°	364.0
25°	326.9
27.5°	290.6
30°	255.8
32.5°	221.0
35°	187.7
37.5°	155.9
40°	125.6
42.5°	97.6
45°	73.4
47.5°	51.5
50°	33.3
52.5°	21.9
55°	18.2
57.5°	15.9
60°	13.6
62.5°	12.1
65°	10.6
67.5°	9.1
70°	7.6
72.5°	6.1
75°	5.3
77.5°	4.5
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)