

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285980

Luminaire Tested: P3AS13R70B2750DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 553.0 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285980

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285980

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96	95	94		92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86		84
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79		77
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79	76	73		71
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74	70	67		65
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70	65	62		61
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66	61	58		56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54		52
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58	54	50		49
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55	51	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129705
5°	127338
10°	120060
15°	108968
20°	95325
25°	80400
30°	65833
35°	51076
40°	36554
45°	23134
50°	11531
55°	7073
60°	6052
65°	5604
70°	4937
75°	4575
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23134 cd/sqm

TEST NUMBER: P1285980

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	9.8
10°-20°	133.6	24.2
20°-30°	152.1	27.5
30°-40°	119.0	21.5
40°-50°	58.4	10.6
50°-60°	18.0	3.3
60°-70°	10.6	1.9
70°-80°	5.7	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.7	61.4
0°-40°	458.6	82.9
0°-60°	535.0	96.7
0°-90°	553.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	553.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	592	
5°	578	54
15°	480	134
25°	332	152
35°	191	119
45°	75	58
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1285980

CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	591.5
2.5°	588.5
5°	578.5
7.5°	562.3
10°	539.2
12.5°	512.3
15°	480.0
17.5°	445.4
20°	408.5
22.5°	370.0
25°	332.3
27.5°	295.4
30°	260.0
32.5°	224.6
35°	190.8
37.5°	158.5
40°	127.7
42.5°	99.2
45°	74.6
47.5°	52.3
50°	33.8
52.5°	22.3
55°	18.5
57.5°	16.2
60°	13.8
62.5°	12.3
65°	10.8
67.5°	9.2
70°	7.7
72.5°	6.2
75°	5.4
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)