

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285171

Luminaire Tested: P3AS13R45B2750DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3CB1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1101.0 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285171

CATALOG NUMBER: P3AS13R45B2750DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285171

CATALOG NUMBER: P3AS13R45B2750DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97		95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92		91
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		92	90	88		87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		88	86	84		82
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		85	82	80		79
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		82	79	76		75
7	90	83	78	74	89	82	78	74	81	77	74		80	76	74		79	76	73		72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76	73	70		69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		73	70	67		66
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71	67	65		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	477352
5°	479880
10°	465144
15°	389787
20°	297969
25°	181390
30°	75480
35°	24173
40°	7528
45°	1520
50°	1126
55°	1262
60°	1096
65°	1297
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1520 cd/sqm

TEST NUMBER: P1285171

CATALOG NUMBER: P3AS13R45B2750DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.6	18.7
10°-20°	471.9	42.9
20°-30°	339.8	30.9
30°-40°	70.7	6.4
40°-50°	6.5	0.6
50°-60°	2.7	0.2
60°-70°	2.1	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1017.3	92.4
0°-40°	1088.0	98.8
0°-60°	1097.1	99.7
0°-90°	1101.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1101.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2177	
5°	2180	206
15°	1717	472
25°	750	340
35°	90	71
45°	5	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1285171

CATALOG NUMBER: P3AS13R45B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2176.9
2.5°	2177.7
5°	2180.1
7.5°	2164.5
10°	2089.0
12.5°	1931.3
15°	1717.0
17.5°	1497.8
20°	1276.9
22.5°	1023.1
25°	749.7
27.5°	494.3
30°	298.1
32.5°	166.7
35°	90.3
37.5°	50.9
40°	26.3
42.5°	11.5
45°	4.9
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.5
60°	2.5
62.5°	2.5
65°	2.5
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)