

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286049

Luminaire Tested: P3AS02R209030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209030D2WDE010 E3PHLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 159.0 lumens
Efficiency: N/A
Efficacy: 22.1 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286049
CATALOG NUMBER: P3AS02R209030D2WDE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1286049

CATALOG NUMBER: P3AS02R209030D2WDE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	52	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56552
5°	52740
10°	43753
15°	33462
20°	25109
25°	18920
30°	13977
35°	9771
40°	6698
45°	4652
50°	3991
55°	3938
60°	4122
65°	4151
70°	4231
75°	4321
80°	4672
85°	4780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 5544 cd/sqm



TEST NUMBER: P1286049

CATALOG NUMBER: P3AS02R209030D2WDE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.5	13.5
10°-20°	41.0	25.8
20°-30°	36.1	22.7
30°-40°	23.3	14.6
40°-50°	12.3	7.8
50°-60°	9.3	5.8
60°-70°	7.9	5.0
70°-80°	5.6	3.5
80°-90°	2.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.5	61.9
0°-40°	121.8	76.6
0°-60°	143.4	90.2
0°-90°	159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	258	
5°	240	21
15°	147	41
25°	78	36
35°	36	23
45°	15	12
55°	10	9
65°	8	8
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1286049
CATALOG NUMBER: P3AS02R209030D2WDE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	257.9
2.5°	252.7
5°	239.6
7.5°	219.5
10°	196.5
12.5°	171.3
15°	147.4
17.5°	125.9
20°	107.6
22.5°	92.2
25°	78.2
27.5°	66.0
30°	55.2
32.5°	45.4
35°	36.5
37.5°	29.5
40°	23.4
42.5°	18.7
45°	15.0
47.5°	13.1
50°	11.7
52.5°	10.8
55°	10.3
57.5°	9.8
60°	9.4
62.5°	8.4
65°	8.0
67.5°	7.5
70°	6.6
72.5°	6.1
75°	5.1
77.5°	4.7
80°	3.7
82.5°	3.3
85°	1.9
87.5°	0.9
90°	0.0

(END OF REPORT)