

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286060

Luminaire Tested: P3AS02R259030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286060
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 440.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286060

CATALOG NUMBER: P3AS02R259030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286060

CATALOG NUMBER: P3AS02R259030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	481891
5°	446400
10°	345373
15°	164973
20°	54395
25°	22937
30°	8887
35°	3855
40°	1288
45°	589
50°	205
55°	115
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 589 cd/sqm

TEST NUMBER: P1286060

CATALOG NUMBER: P3AS02R259030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	40.5
10°-20°	202.7	46.1
20°-30°	47.1	10.7
30°-40°	9.9	2.2
40°-50°	1.6	0.4
50°-60°	0.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.1	97.3
0°-40°	438.0	99.5
0°-60°	439.9	100.0
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2198	
5°	2028	178
15°	727	203
25°	95	47
35°	14	10
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1286060

CATALOG NUMBER: P3AS02R259030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2197.6
1°	2193.1
2°	2170.3
3°	2138.2
4°	2089.2
5°	2028.0
6°	1949.3
7°	1867.0
8°	1774.6
9°	1670.5
10°	1551.1
11°	1412.8
12°	1254.1
13°	1080.2
14°	898.3
15°	726.7
16°	574.8
17°	447.8
18°	352.2
19°	281.7
20°	233.1
21°	194.8
22°	163.5
23°	136.6
24°	114.2
25°	94.8
27.5°	56.2
30°	35.1
32.5°	22.5
35°	14.4
37.5°	8.6
40°	4.5
42.5°	2.9
45°	1.9
47.5°	1.1
50°	0.6
52.5°	0.3
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0



TEST NUMBER: P1286060

CATALOG NUMBER: P3AS02R259030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)