

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285253

Luminaire Tested: P3AS13R45B2750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 656.0 lumens
Efficiency: N/A
Efficacy: 34.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285253

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285253

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139090
5°	136627
10°	129278
15°	117912
20°	104262
25°	90537
30°	77708
35°	64755
40°	48262
45°	29553
50°	13680
55°	10705
60°	10262
65°	9391
70°	8719
75°	8303
80°	7577
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29553 cd/sqm

TEST NUMBER: P1285253

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	8.8
10°-20°	144.6	22.0
20°-30°	171.8	26.2
30°-40°	149.3	22.8
40°-50°	74.9	11.4
50°-60°	26.0	4.0
60°-70°	18.2	2.8
70°-80°	10.2	1.5
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.4	57.1
0°-40°	523.7	79.8
0°-60°	624.5	95.2
0°-90°	656.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	656.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	621	58
15°	519	145
25°	374	172
35°	242	149
45°	95	75
55°	28	26
65°	18	18
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1285253

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	634.3
2.5°	631.3
5°	620.7
7.5°	604.0
10°	580.6
12.5°	551.9
15°	519.4
17.5°	483.1
20°	446.8
22.5°	409.8
25°	374.2
27.5°	340.2
30°	306.9
32.5°	275.2
35°	241.9
37.5°	206.4
40°	168.6
42.5°	131.5
45°	95.3
47.5°	62.7
50°	40.1
52.5°	31.0
55°	28.0
57.5°	25.7
60°	23.4
62.5°	21.2
65°	18.1
67.5°	15.9
70°	13.6
72.5°	11.3
75°	9.8
77.5°	7.6
80°	6.0
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)