

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286078

Luminaire Tested: P3AS02R259030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 209.0 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286078

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286078

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75871
5°	72793
10°	63771
15°	51260
20°	39390
25°	29808
30°	21522
35°	14295
40°	8673
45°	5055
50°	3207
55°	2600
60°	2281
65°	2024
70°	1667
75°	1694
80°	1263
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5055 cd/sqm

TEST NUMBER: P1286078

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.1	14.4
10°-20°	62.4	29.9
20°-30°	56.5	27.0
30°-40°	33.9	16.2
40°-50°	13.5	6.5
50°-60°	6.2	3.0
60°-70°	3.8	1.8
70°-80°	2.0	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.0	71.3
0°-40°	182.9	87.5
0°-60°	202.6	96.9
0°-90°	209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	209.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	346	
5°	331	30
15°	226	62
25°	123	56
35°	53	34
45°	16	13
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1286078

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	346.0
1°	346.0
2°	344.4
3°	340.8
4°	336.3
5°	330.7
6°	323.6
7°	315.4
8°	306.0
9°	296.5
10°	286.4
11°	274.7
12°	262.6
13°	250.6
14°	238.5
15°	225.8
17.5°	195.8
20°	168.8
22.5°	144.3
25°	123.2
27.5°	103.3
30°	85.0
32.5°	68.4
35°	53.4
37.5°	40.7
40°	30.3
42.5°	22.2
45°	16.3
47.5°	12.4
50°	9.4
52.5°	7.8
55°	6.8
57.5°	5.9
60°	5.2
62.5°	4.2
65°	3.9
67.5°	3.3
70°	2.6
72.5°	2.3
75°	2.0
77.5°	1.6
80°	1.0
82.5°	0.7
85°	0.7
87.5°	0.3



TEST NUMBER: P1286078

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)