

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285280

Luminaire Tested: P3AS13R45B2750DE010 E3DLP1WH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1285280  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R45B2750DE010 E3DLP1WH\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 860.0 lumens  
Efficiency: N/A  
Efficacy: 45.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285280  
CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1285280  
 CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	322957
5°	315385
10°	289930
15°	245654
20°	190603
25°	133242
30°	83937
35°	49416
40°	27967
45°	13583
50°	4708
55°	3823
60°	3728
65°	3580
70°	3462
75°	3219
80°	2904
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13583 cd/sqm



TEST NUMBER: P1285280  
 CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.6	15.4
10°-20°	297.2	34.6
20°-30°	252.3	29.3
30°-40°	120.4	14.0
40°-50°	36.2	4.2
50°-60°	9.2	1.1
60°-70°	6.9	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	682.1	79.3
0°-40°	802.5	93.3
0°-60°	847.9	98.6
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1473	
5°	1433	133
15°	1082	297
25°	551	252
35°	185	120
45°	44	36
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1285280  
CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1472.8
2.5°	1463.6
5°	1432.8
7.5°	1379.8
10°	1302.1
12.5°	1199.0
15°	1082.1
17.5°	952.1
20°	816.8
22.5°	679.1
25°	550.7
27.5°	433.8
30°	331.5
32.5°	249.2
35°	184.6
37.5°	136.1
40°	97.7
42.5°	67.7
45°	43.8
47.5°	24.6
50°	13.8
52.5°	10.8
55°	10.0
57.5°	9.2
60°	8.5
62.5°	7.7
65°	6.9
67.5°	6.2
70°	5.4
72.5°	4.6
75°	3.8
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)