

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286093

Luminaire Tested: P3AS02R309030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286093
CATALOG NUMBER: P3AS02R309030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1286093
 CATALOG NUMBER: P3AS02R309030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	81	78	76	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	79	75	73	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	76	72	70	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	73	70	67	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98611
5°	93858
10°	78956
15°	56936
20°	35306
25°	20082
30°	11166
35°	6077
40°	3206
45°	1737
50°	921
55°	612
60°	570
65°	571
70°	513
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1737 cd/sqm



TEST NUMBER: P1286093

CATALOG NUMBER: P3AS02R309030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	22.7
10°-20°	68.3	40.4
20°-30°	39.4	23.3
30°-40°	15.0	8.9
40°-50°	4.6	2.7
50°-60°	1.5	0.9
60°-70°	1.1	0.6
70°-80°	0.6	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	146.1	86.4
0°-40°	161.1	95.3
0°-60°	167.2	98.9
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	426	38
15°	251	68
25°	83	39
35°	23	15
45°	6	5
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1286093
CATALOG NUMBER: P3AS02R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	449.7
1°	449.4
2°	446.7
3°	441.6
4°	435.2
5°	426.4
6°	415.2
7°	402.8
8°	388.9
9°	372.3
10°	354.6
11°	335.4
12°	315.1
13°	293.9
14°	272.4
15°	250.8
17.5°	197.8
20°	151.3
22.5°	112.2
25°	83.0
27.5°	60.3
30°	44.1
32.5°	31.8
35°	22.7
37.5°	15.8
40°	11.2
42.5°	7.8
45°	5.6
47.5°	3.8
50°	2.7
52.5°	1.9
55°	1.6
57.5°	1.4
60°	1.3
62.5°	1.1
65°	1.1
67.5°	1.0
70°	0.8
72.5°	0.6
75°	0.5
77.5°	0.5
80°	0.3
82.5°	0.3
85°	0.2
87.5°	0.0



TEST NUMBER: P1286093
CATALOG NUMBER: P3AS02R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)