

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285286

Luminaire Tested: P3AS13R45B2750DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 592.0 lumens
Efficiency: N/A
Efficacy: 31.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285286

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285286

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	86
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86	83	81	79
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75	74
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77	73	70	69
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73	69	66	64
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69	65	61	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	56
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176324
5°	172309
10°	158959
15°	138230
20°	113550
25°	88336
30°	65251
35°	45909
40°	28654
45°	15536
50°	8392
55°	7226
60°	6491
65°	5552
70°	4744
75°	4829
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15536 cd/sqm

TEST NUMBER: P1285286

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	12.2
10°-20°	168.3	28.4
20°-30°	167.1	28.2
30°-40°	107.6	18.2
40°-50°	41.4	7.0
50°-60°	16.9	2.8
60°-70°	10.7	1.8
70°-80°	5.7	1.0
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	407.9	68.9
0°-40°	515.5	87.1
0°-60°	573.8	96.9
0°-90°	592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	783	73
15°	609	168
25°	365	167
35°	172	108
45°	50	41
55°	19	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1285286

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	804.1
2.5°	800.0
5°	782.8
7.5°	753.3
10°	713.9
12.5°	664.7
15°	608.9
17.5°	548.1
20°	486.6
22.5°	424.2
25°	365.1
27.5°	309.3
30°	257.7
32.5°	212.5
35°	171.5
37.5°	134.6
40°	100.1
42.5°	72.2
45°	50.1
47.5°	33.6
50°	24.6
52.5°	20.5
55°	18.9
57.5°	16.4
60°	14.8
62.5°	12.3
65°	10.7
67.5°	9.0
70°	7.4
72.5°	6.6
75°	5.7
77.5°	4.1
80°	3.3
82.5°	2.5
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)