

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285296

Luminaire Tested: P3AS13R50B2750DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3CB1MMS_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 80CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1124.0 lumens
Efficiency: N/A
Efficacy: 58.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285296

CATALOG NUMBER: P3AS13R50B2750DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285296

CATALOG NUMBER: P3AS13R50B2750DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391460
5°	384459
10°	369131
15°	338504
20°	298483
25°	228787
30°	124399
35°	40020
40°	9418
45°	1271
50°	1126
55°	1262
60°	1096
65°	1297
70°	1026
75°	1356
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 2013 cd/sqm

TEST NUMBER: P1285296

CATALOG NUMBER: P3AS13R50B2750DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.9	14.6
10°-20°	414.5	36.9
20°-30°	415.1	36.9
30°-40°	116.7	10.4
40°-50°	7.1	0.6
50°-60°	2.7	0.2
60°-70°	2.1	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	993.5	88.4
0°-40°	1110.2	98.8
0°-60°	1119.9	99.6
0°-90°	1124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1785	
5°	1747	164
15°	1491	414
25°	946	415
35°	150	117
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1285296

CATALOG NUMBER: P3AS13R50B2750DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1785.2
2.5°	1776.1
5°	1746.6
7.5°	1706.3
10°	1657.8
12.5°	1584.7
15°	1491.1
17.5°	1383.5
20°	1279.1
22.5°	1149.3
25°	945.6
27.5°	704.0
30°	491.3
32.5°	296.6
35°	149.5
37.5°	70.7
40°	32.9
42.5°	12.3
45°	4.1
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.5
60°	2.5
62.5°	2.5
65°	2.5
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)