

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286130

Luminaire Tested: P3AS02R359030D2WDE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286130
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359030D2WDE010 E3DLD1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 262.9 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286130
CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1286130

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60083
5°	58794
10°	55065
15°	49421
20°	43007
25°	36631
30°	30688
35°	24440
40°	17662
45°	11195
50°	6106
55°	4205
60°	3991
65°	3684
70°	3526
75°	3050
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11195 cd/sqm



TEST NUMBER: P1286130

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	9.5
10°-20°	60.6	23.0
20°-30°	69.4	26.4
30°-40°	56.7	21.5
40°-50°	28.6	10.9
50°-60°	10.6	4.0
60°-70°	7.1	2.7
70°-80°	3.9	1.5
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	154.9	58.9
0°-40°	211.6	80.5
0°-60°	250.7	95.4
0°-90°	262.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	262.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	267	25
15°	218	61
25°	151	69
35°	91	57
45°	36	29
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1286130
CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.0
1°	273.6
2°	273.0
3°	271.7
4°	269.7
5°	267.1
6°	263.9
7°	260.6
8°	256.4
9°	252.2
10°	247.3
11°	242.1
12°	236.6
13°	230.4
14°	223.9
15°	217.7
17.5°	201.2
20°	184.3
22.5°	167.0
25°	151.4
27.5°	136.2
30°	121.2
32.5°	106.3
35°	91.3
37.5°	76.4
40°	61.7
42.5°	48.1
45°	36.1
47.5°	26.0
50°	17.9
52.5°	13.0
55°	11.0
57.5°	10.1
60°	9.1
62.5°	8.1
65°	7.1
67.5°	6.2
70°	5.5
72.5°	4.5
75°	3.6
77.5°	2.9
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.6



TEST NUMBER: P1286130
CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)