

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286131

Luminaire Tested: P3AS02R359030D2WDE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286131
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359030D2WDE010 E3DLD1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 262.9 lumens
Efficiency: N/A
Efficacy: 36.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286131

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1286131

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96	94	93
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89	87	85
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	78
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68	64	61
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64	60	56
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61	56	52
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60083
5°	58794
10°	55065
15°	49421
20°	43007
25°	36631
30°	30688
35°	24440
40°	17662
45°	11195
50°	6106
55°	4205
60°	3991
65°	3684
70°	3526
75°	3050
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 11195 cd/sqm

TEST NUMBER: P1286131

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	9.5
10°-20°	60.6	23.0
20°-30°	69.4	26.4
30°-40°	56.7	21.5
40°-50°	28.6	10.9
50°-60°	10.6	4.0
60°-70°	7.1	2.7
70°-80°	3.9	1.5
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	154.9	58.9
0°-40°	211.6	80.5
0°-60°	250.7	95.4
0°-90°	262.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	262.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	267	25
15°	218	61
25°	151	69
35°	91	57
45°	36	29
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286131

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.0
1°	273.6
2°	273.0
3°	271.7
4°	269.7
5°	267.1
6°	263.9
7°	260.6
8°	256.4
9°	252.2
10°	247.3
11°	242.1
12°	236.6
13°	230.4
14°	223.9
15°	217.7
17.5°	201.2
20°	184.3
22.5°	167.0
25°	151.4
27.5°	136.2
30°	121.2
32.5°	106.3
35°	91.3
37.5°	76.4
40°	61.7
42.5°	48.1
45°	36.1
47.5°	26.0
50°	17.9
52.5°	13.0
55°	11.0
57.5°	10.1
60°	9.1
62.5°	8.1
65°	7.1
67.5°	6.2
70°	5.5
72.5°	4.5
75°	3.6
77.5°	2.9
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.6



TEST NUMBER: P1286131

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)