

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286152

Luminaire Tested: P3AS02R409030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286152
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 456.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286152

CATALOG NUMBER: P3AS02R409030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286152

CATALOG NUMBER: P3AS02R409030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96	95	94	92
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93	91	90	88
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90	88	86	85
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88	85	83	82
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85	82	80	79
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82	79	77	76
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79	76	74	73
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77	74	71	70
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74	71	69	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232438
5°	230750
10°	224712
15°	200728
20°	133105
25°	49866
30°	13344
35°	5220
40°	1861
45°	899
50°	273
55°	115
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 899 cd/sqm

TEST NUMBER: P1286152

CATALOG NUMBER: P3AS02R409030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.9	21.7
10°-20°	234.3	51.4
20°-30°	106.2	23.3
30°-40°	13.8	3.0
40°-50°	2.4	0.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.5	96.4
0°-40°	453.2	99.4
0°-60°	455.9	100.0
0°-90°	456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	456.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1060	
5°	1048	99
15°	884	234
25°	206	106
35°	20	14
45°	3	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1286152

CATALOG NUMBER: P3AS02R409030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1060.0
1°	1059.3
2°	1057.7
3°	1055.4
4°	1052.3
5°	1048.3
6°	1043.7
7°	1038.0
8°	1030.9
9°	1021.4
10°	1009.2
11°	995.0
12°	976.0
13°	952.5
14°	921.9
15°	884.2
16°	836.2
17°	781.4
18°	715.6
19°	646.2
20°	570.4
21°	494.6
22°	419.8
23°	345.5
24°	272.3
25°	206.1
26°	152.6
27°	111.7
28°	84.0
29°	65.3
30°	52.7
31°	43.6
32°	36.4
32.5°	33.2
33°	30.0
34°	24.4
35°	19.5
36°	15.3
37°	12.1
37.5°	10.9
38°	9.6
39°	8.0
40°	6.5
42.5°	4.3
45°	2.9



TEST NUMBER: P1286152

CATALOG NUMBER: P3AS02R409030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.8
50°	0.8
52.5°	0.3
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)