

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285378

Luminaire Tested: P3AS13R50B2750DE010 E3DLD1H\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50B2750DE010 E3DLD1H\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 661.9 lumens  
Efficiency: N/A  
Efficacy: 34.7 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285378

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1H\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1285378

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1H\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 95  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 4   | 93  | 85  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 65  | 60  |  | 69  | 64  | 60  |  | 67  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 51  |  | 59  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 52  | 48  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  |  | 54  | 48  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 134529 |
| 5°  | 132555 |
| 10° | 126673 |
| 15° | 117322 |
| 20° | 105429 |
| 25° | 92691  |
| 30° | 78822  |
| 35° | 63925  |
| 40° | 48004  |
| 45° | 30918  |
| 50° | 14703  |
| 55° | 11546  |
| 60° | 10920  |
| 65° | 10170  |
| 70° | 9232   |
| 75° | 8303   |
| 80° | 7577   |
| 85° | 7548   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30918 cd/sqm

TEST NUMBER: P1285378

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1H\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 56.4   | 8.5       |
| 10°-20°   | 144.1  | 21.8      |
| 20°-30°   | 175.1  | 26.4      |
| 30°-40°   | 148.5  | 22.4      |
| 40°-50°   | 77.1   | 11.6      |
| 50°-60°   | 27.8   | 4.2       |
| 60°-70°   | 19.2   | 2.9       |
| 70°-80°   | 10.5   | 1.6       |
| 80°-90°   | 3.3    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 375.6  | 56.7      |
| 0°-40°    | 524.1  | 79.2      |
| 0°-60°    | 629.0  | 95.0      |
| 0°-90°    | 661.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 661.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 614 |      |
| 5°  | 602 | 56   |
| 15° | 517 | 144  |
| 25° | 383 | 175  |
| 35° | 239 | 148  |
| 45° | 100 | 77   |
| 55° | 30  | 28   |
| 65° | 20  | 19   |
| 75° | 10  | 10   |
| 85° | 3   | 3    |
| 90° | 0   |      |



TEST NUMBER: P1285378

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 613.5 |
| 2.5°  | 611.2 |
| 5°    | 602.2 |
| 7.5°  | 588.6 |
| 10°   | 568.9 |
| 12.5° | 544.0 |
| 15°   | 516.8 |
| 17.5° | 485.8 |
| 20°   | 451.8 |
| 22.5° | 417.1 |
| 25°   | 383.1 |
| 27.5° | 347.6 |
| 30°   | 311.3 |
| 32.5° | 275.0 |
| 35°   | 238.8 |
| 37.5° | 203.2 |
| 40°   | 167.7 |
| 42.5° | 133.7 |
| 45°   | 99.7  |
| 47.5° | 66.5  |
| 50°   | 43.1  |
| 52.5° | 33.2  |
| 55°   | 30.2  |
| 57.5° | 27.2  |
| 60°   | 24.9  |
| 62.5° | 21.9  |
| 65°   | 19.6  |
| 67.5° | 16.6  |
| 70°   | 14.4  |
| 72.5° | 12.1  |
| 75°   | 9.8   |
| 77.5° | 7.6   |
| 80°   | 6.0   |
| 82.5° | 4.5   |
| 85°   | 3.0   |
| 87.5° | 1.5   |
| 90°   | 0.0   |

(END OF REPORT)