

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286155

Luminaire Tested: P3AS02R409030D2WDE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409030D2WDE010 E3DL1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 379.1 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286155

CATALOG NUMBER: P3AS02R409030D2WDE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286155

CATALOG NUMBER: P3AS02R409030D2WDE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	92	91
3	104	99	94	91		102	97	93	90		95	91	88		92	89	87		90	88	86
4	100	93	88	85		98	92	88	84		90	86	83		88	85	82		86	84	81
5	96	88	83	79		94	88	83	79		86	82	78		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	77	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	68		84	76	71	67		75	70	67		74	70	67		73	69	67
9	82	73	68	64		81	73	68	64		72	67	64		71	67	64		70	66	64
10	78	70	65	62		78	70	65	61		69	64	61		68	64	61		67	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167706
5°	162822
10°	147759
15°	122067
20°	88068
25°	54463
30°	29498
35°	15232
40°	8301
45°	4652
50°	2320
55°	1759
60°	1579
65°	1505
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4652 cd/sqm

TEST NUMBER: P1286155

CATALOG NUMBER: P3AS02R409030D2WDE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	18.0
10°-20°	146.4	38.6
20°-30°	104.5	27.6
30°-40°	38.5	10.1
40°-50°	12.1	3.2
50°-60°	4.2	1.1
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.1	84.2
0°-40°	357.6	94.3
0°-60°	373.9	98.6
0°-90°	379.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	379.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	765	
5°	740	68
15°	538	146
25°	225	105
35°	57	38
45°	15	12
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286155

CATALOG NUMBER: P3AS02R409030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	764.8
2.5°	758.9
5°	739.7
7.5°	707.9
10°	663.6
12.5°	607.3
15°	537.7
17.5°	459.7
20°	377.4
22.5°	296.4
25°	225.1
27.5°	165.3
30°	116.5
32.5°	81.7
35°	56.9
37.5°	40.3
40°	29.0
42.5°	20.8
45°	15.0
47.5°	10.1
50°	6.8
52.5°	4.9
55°	4.6
57.5°	4.2
60°	3.6
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)