

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285388

Luminaire Tested: P3AS13R50B2750DE010 E3DLD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLD1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 661.9 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285388
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285388
 CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69		
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63		
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53		
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134529
5°	132555
10°	126673
15°	117322
20°	105429
25°	92691
30°	78822
35°	63925
40°	48004
45°	30918
50°	14703
55°	11546
60°	10920
65°	10170
70°	9232
75°	8303
80°	7577
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30918 cd/sqm



TEST NUMBER: P1285388

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	8.5
10°-20°	144.1	21.8
20°-30°	175.1	26.4
30°-40°	148.5	22.4
40°-50°	77.1	11.6
50°-60°	27.8	4.2
60°-70°	19.2	2.9
70°-80°	10.5	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	375.6	56.7
0°-40°	524.1	79.2
0°-60°	629.0	95.0
0°-90°	661.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	602	56
15°	517	144
25°	383	175
35°	239	148
45°	100	77
55°	30	28
65°	20	19
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1285388
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	613.5
2.5°	611.2
5°	602.2
7.5°	588.6
10°	568.9
12.5°	544.0
15°	516.8
17.5°	485.8
20°	451.8
22.5°	417.1
25°	383.1
27.5°	347.6
30°	311.3
32.5°	275.0
35°	238.8
37.5°	203.2
40°	167.7
42.5°	133.7
45°	99.7
47.5°	66.5
50°	43.1
52.5°	33.2
55°	30.2
57.5°	27.2
60°	24.9
62.5°	21.9
65°	19.6
67.5°	16.6
70°	14.4
72.5°	12.1
75°	9.8
77.5°	7.6
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)