

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285400

Luminaire Tested: P3AS13R50B2750DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 674.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285400
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285400

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	8.5
10°-20°	146.7	21.8
20°-30°	178.2	26.4
30°-40°	151.2	22.4
40°-50°	78.5	11.6
50°-60°	28.3	4.2
60°-70°	19.6	2.9
70°-80°	10.7	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.4	56.7
0°-40°	533.6	79.2
0°-60°	640.4	95.0
0°-90°	674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	674.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	625	
5°	613	57
15°	526	147
25°	390	178
35°	243	151
45°	102	79
55°	31	28
65°	20	20
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P1285400
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	624.6
2.5°	622.3
5°	613.1
7.5°	599.2
10°	579.2
12.5°	553.9
15°	526.2
17.5°	494.6
20°	460.0
22.5°	424.6
25°	390.0
27.5°	353.9
30°	316.9
32.5°	280.0
35°	243.1
37.5°	206.9
40°	170.8
42.5°	136.2
45°	101.5
47.5°	67.7
50°	43.8
52.5°	33.8
55°	30.8
57.5°	27.7
60°	25.4
62.5°	22.3
65°	20.0
67.5°	16.9
70°	14.6
72.5°	12.3
75°	10.0
77.5°	7.7
80°	6.2
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)