

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285405

Luminaire Tested: P3AS13R50B2750DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285405
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 278.1 lumens
Efficiency: N/A
Efficacy: 14.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285405

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285405

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	95	94		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87		85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81		79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81	78	75		73
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76	73	70		68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65		64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68	64	61		60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57		56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54		53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59	54	51		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80849
5°	78670
10°	72544
15°	63814
20°	53391
25°	42341
30°	31068
35°	21362
40°	13568
45°	7598
50°	4094
55°	3441
60°	2982
65°	2750
70°	2436
75°	2203
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7598 cd/sqm

TEST NUMBER: P1285405

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.1	11.9
10°-20°	77.8	28.0
20°-30°	79.6	28.6
30°-40°	50.5	18.2
40°-50°	20.1	7.2
50°-60°	8.1	2.9
60°-70°	5.2	1.9
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	190.6	68.5
0°-40°	241.1	86.7
0°-60°	269.3	96.9
0°-90°	278.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	369	
5°	357	33
15°	281	78
25°	175	80
35°	80	51
45°	24	20
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1285405

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	368.7
2.5°	366.1
5°	357.4
7.5°	343.9
10°	325.8
12.5°	304.4
15°	281.1
17.5°	255.5
20°	228.8
22.5°	202.0
25°	175.0
27.5°	147.9
30°	122.7
32.5°	100.1
35°	79.8
37.5°	62.5
40°	47.4
42.5°	35.0
45°	24.5
47.5°	16.6
50°	12.0
52.5°	10.2
55°	9.0
57.5°	7.9
60°	6.8
62.5°	6.0
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.0
75°	2.6
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)