

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286178

Luminaire Tested: P3AS02R459030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 178.1 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286178

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286178

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66837
5°	65287
10°	60008
15°	50852
20°	39460
25°	27582
30°	17370
35°	10226
40°	5782
45°	2822
50°	989
55°	803
60°	789
65°	726
70°	705
75°	678
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2822 cd/sqm

TEST NUMBER: P1286178

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.5	15.4
10°-20°	61.5	34.5
20°-30°	52.2	29.3
30°-40°	24.9	14.0
40°-50°	7.5	4.2
50°-60°	1.9	1.1
60°-70°	1.4	0.8
70°-80°	0.8	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	141.2	79.3
0°-40°	166.1	93.3
0°-60°	175.5	98.6
0°-90°	178.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	305	
5°	297	27
15°	224	62
25°	114	52
35°	38	25
45°	9	8
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286178

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	304.8
2.5°	302.9
5°	296.6
7.5°	285.6
10°	269.5
12.5°	248.2
15°	224.0
17.5°	197.1
20°	169.1
22.5°	140.6
25°	114.0
27.5°	89.8
30°	68.6
32.5°	51.6
35°	38.2
37.5°	28.2
40°	20.2
42.5°	14.0
45°	9.1
47.5°	5.1
50°	2.9
52.5°	2.2
55°	2.1
57.5°	1.9
60°	1.8
62.5°	1.6
65°	1.4
67.5°	1.3
70°	1.1
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)