

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286181

Luminaire Tested: P3AS02R459030D2WDE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030D2WDE010 E3DL1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DL1M
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 364.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286181

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1286181

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136700
5°	133502
10°	122710
15°	103973
20°	80670
25°	56398
30°	35524
35°	20907
40°	11822
45°	5768
50°	2013
55°	1606
60°	1579
65°	1505
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5768 cd/sqm

TEST NUMBER: P1286181

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	15.4
10°-20°	125.8	34.6
20°-30°	106.8	29.3
30°-40°	50.9	14.0
40°-50°	15.3	4.2
50°-60°	3.9	1.1
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.7	79.3
0°-40°	339.7	93.3
0°-60°	358.9	98.6
0°-90°	364.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	364.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	623	
5°	606	56
15°	458	126
25°	233	107
35°	78	51
45°	19	15
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286181

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	623.4
2.5°	619.5
5°	606.5
7.5°	584.0
10°	551.1
12.5°	507.5
15°	458.0
17.5°	403.0
20°	345.7
22.5°	287.4
25°	233.1
27.5°	183.6
30°	140.3
32.5°	105.5
35°	78.1
37.5°	57.6
40°	41.3
42.5°	28.6
45°	18.6
47.5°	10.4
50°	5.9
52.5°	4.6
55°	4.2
57.5°	3.9
60°	3.6
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)