

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286189

Luminaire Tested: P3AS02R459030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 281.9 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286189

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286189

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	91	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59798
5°	58728
10°	55577
15°	50693
20°	44827
25°	38930
30°	33398
35°	27840
40°	20753
45°	12683
50°	5868
55°	4588
60°	4429
65°	4047
70°	3719
75°	3558
80°	3283
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12683 cd/sqm

TEST NUMBER: P1286189

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	8.8
10°-20°	62.2	22.1
20°-30°	73.8	26.2
30°-40°	64.2	22.8
40°-50°	32.2	11.4
50°-60°	11.2	4.0
60°-70°	7.8	2.8
70°-80°	4.4	1.5
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.9	57.1
0°-40°	225.1	79.9
0°-60°	268.4	95.2
0°-90°	281.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	273	
5°	267	25
15°	223	62
25°	161	74
35°	104	64
45°	41	32
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286189

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	272.7
2.5°	271.4
5°	266.8
7.5°	259.7
10°	249.6
12.5°	237.2
15°	223.3
17.5°	207.7
20°	192.1
22.5°	176.1
25°	160.9
27.5°	146.2
30°	131.9
32.5°	118.3
35°	104.0
37.5°	88.7
40°	72.5
42.5°	56.5
45°	40.9
47.5°	27.0
50°	17.2
52.5°	13.3
55°	12.0
57.5°	11.0
60°	10.1
62.5°	9.1
65°	7.8
67.5°	6.8
70°	5.8
72.5°	4.9
75°	4.2
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.0
87.5°	0.6
90°	0.0

(END OF REPORT)