

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286192

Luminaire Tested: P3AS02R459030D2WDE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286192  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459030D2WDE010 E3DLP1LI  
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 235.0 lumens  
Efficiency: N/A  
Efficacy: 32.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286192  
CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1286192  
 CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	62	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	69994
5°	68391
10°	63103
15°	54870
20°	45084
25°	35058
30°	25903
35°	18230
40°	11364
45°	6171
50°	3343
55°	2867
60°	2588
65°	2179
70°	1859
75°	1949
80°	1642
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6171 cd/sqm



TEST NUMBER: P1286192

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.8	12.2
10°-20°	66.8	28.4
20°-30°	66.3	28.2
30°-40°	42.7	18.2
40°-50°	16.5	7.0
50°-60°	6.7	2.8
60°-70°	4.2	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.9	68.9
0°-40°	204.6	87.1
0°-60°	227.8	96.9
0°-90°	235.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	235.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	319	
5°	311	29
15°	242	67
25°	145	66
35°	68	43
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1286192

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	319.2
2.5°	317.6
5°	310.7
7.5°	299.0
10°	283.4
12.5°	263.8
15°	241.7
17.5°	217.6
20°	193.2
22.5°	168.4
25°	144.9
27.5°	122.8
30°	102.3
32.5°	84.4
35°	68.1
37.5°	53.4
40°	39.7
42.5°	28.7
45°	19.9
47.5°	13.4
50°	9.8
52.5°	8.1
55°	7.5
57.5°	6.5
60°	5.9
62.5°	4.9
65°	4.2
67.5°	3.6
70°	2.9
72.5°	2.6
75°	2.3
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)