

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286232

Luminaire Tested: P3AS02R559030D2WDE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559030D2WDE010 E3D1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 420.1 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286232
CATALOG NUMBER: P3AS02R559030D2WDE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1286232
 CATALOG NUMBER: P3AS02R559030D2WDE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	65	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121788
5°	117477
10°	121686
15°	119978
20°	111030
25°	89787
30°	53806
35°	18230
40°	5038
45°	2233
50°	648
55°	115
60°	88
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2233 cd/sqm



TEST NUMBER: P1286232
 CATALOG NUMBER: P3AS02R559030D2WDE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	12.3
10°-20°	147.1	35.0
20°-30°	163.5	38.9
30°-40°	50.9	12.1
40°-50°	6.1	1.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.3	86.3
0°-40°	413.2	98.4
0°-60°	419.8	99.9
0°-90°	420.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	555	
5°	534	52
15°	528	147
25°	371	164
35°	68	51
45°	7	6
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1286232
CATALOG NUMBER: P3AS02R559030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	555.4
1°	553.4
2°	547.9
3°	541.2
4°	535.2
5°	533.7
6°	535.3
7°	538.7
8°	542.5
9°	545.5
10°	546.5
11°	545.9
12°	543.3
13°	539.3
14°	534.7
15°	528.5
16°	521.3
17°	512.2
18°	502.0
19°	489.7
20°	475.8
21°	460.0
22°	441.3
23°	420.8
24°	397.1
25°	371.1
26°	342.6
27°	312.3
28°	279.9
29°	246.5
30°	212.5
31°	178.4
32°	145.0
32.5°	130.2
33°	114.9
34°	88.9
35°	68.1
36°	51.9
37°	38.5
37.5°	32.9
38°	28.6
39°	21.7
40°	17.6
42.5°	11.2
45°	7.2



TEST NUMBER: P1286232
CATALOG NUMBER: P3AS02R559030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.3
50°	1.9
52.5°	0.6
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)