

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285501

Luminaire Tested: P3AS13R55B2750DE010 E3DL1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DL1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 895.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285501
CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285501
 CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245770
5°	243275
10°	234932
15°	217141
20°	187383
25°	148000
30°	104978
35°	67699
40°	40648
45°	22917
50°	12315
55°	4396
60°	3947
65°	3840
70°	3654
75°	3474
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22917 cd/sqm



TEST NUMBER: P1285501
 CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	11.6
10°-20°	264.5	29.6
20°-30°	277.2	31.0
30°-40°	161.7	18.1
40°-50°	60.5	6.8
50°-60°	14.2	1.6
60°-70°	7.3	0.8
70°-80°	4.3	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.6	72.1
0°-40°	807.4	90.2
0°-60°	882.1	98.6
0°-90°	895.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1121	
5°	1105	104
15°	956	265
25°	612	277
35°	253	162
45°	74	61
55°	12	14
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1285501
CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1120.8
2.5°	1117.5
5°	1105.2
7.5°	1085.5
10°	1055.1
12.5°	1012.4
15°	956.5
17.5°	885.9
20°	803.0
22.5°	710.2
25°	611.7
27.5°	510.7
30°	414.6
32.5°	327.6
35°	252.9
37.5°	192.1
40°	142.0
42.5°	101.8
45°	73.9
47.5°	53.4
50°	36.1
52.5°	20.5
55°	11.5
57.5°	9.9
60°	9.0
62.5°	8.2
65°	7.4
67.5°	6.6
70°	5.7
72.5°	4.9
75°	4.1
77.5°	3.3
80°	2.5
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)