

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286246

Luminaire Tested: P3AS02R559030D2WDE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1286246  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R559030D2WDE010 E3DLD1WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 274.9 lumens  
Efficiency: N/A  
Efficacy: 38.2 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286246

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DLD1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1286246

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 100 | 98  |  | 99  | 97  | 96  |  | 95  |
| 2   | 105 | 100 | 95  | 91  | 103 | 98  | 93  | 90  | 94  | 91  | 88  |  | 91  | 88  | 86  |  | 89  |
| 3   | 99  | 91  | 85  | 81  | 97  | 90  | 84  | 80  | 87  | 82  | 79  |  | 85  | 81  | 77  |  | 82  |
| 4   | 93  | 84  | 77  | 72  | 91  | 83  | 77  | 72  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 76  |
| 5   | 87  | 77  | 71  | 66  | 85  | 76  | 70  | 65  | 75  | 69  | 65  |  | 73  | 68  | 64  |  | 71  |
| 6   | 82  | 72  | 65  | 60  | 80  | 71  | 64  | 60  | 69  | 64  | 59  |  | 68  | 63  | 59  |  | 66  |
| 7   | 77  | 67  | 60  | 55  | 76  | 66  | 59  | 55  | 65  | 59  | 54  |  | 63  | 58  | 54  |  | 62  |
| 8   | 73  | 62  | 55  | 51  | 72  | 62  | 55  | 51  | 60  | 55  | 50  |  | 59  | 54  | 50  |  | 58  |
| 9   | 69  | 58  | 51  | 47  | 68  | 58  | 51  | 47  | 57  | 51  | 47  |  | 56  | 50  | 46  |  | 55  |
| 10  | 65  | 55  | 48  | 44  | 64  | 54  | 48  | 44  | 53  | 47  | 43  |  | 52  | 47  | 43  |  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 51706 |
| 5°  | 51045 |
| 10° | 49030 |
| 15° | 45857 |
| 20° | 41840 |
| 25° | 37333 |
| 30° | 32638 |
| 35° | 27117 |
| 40° | 21383 |
| 45° | 14513 |
| 50° | 8870  |
| 55° | 4588  |
| 60° | 4254  |
| 65° | 4047  |
| 70° | 3719  |
| 75° | 3304  |
| 80° | 3283  |
| 85° | 2516  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14513 cd/sqm

TEST NUMBER: P1286246

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DLD1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 21.7   | 7.9       |
| 10°-20°   | 56.5   | 20.5      |
| 20°-30°   | 70.7   | 25.7      |
| 30°-40°   | 63.1   | 23.0      |
| 40°-50°   | 37.0   | 13.4      |
| 50°-60°   | 12.8   | 4.6       |
| 60°-70°   | 7.7    | 2.8       |
| 70°-80°   | 4.3    | 1.6       |
| 80°-90°   | 1.2    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 148.9  | 54.2      |
| 0°-40°    | 212.0  | 77.1      |
| 0°-60°    | 261.7  | 95.2      |
| 0°-90°    | 274.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 274.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 236 |      |
| 5°  | 232 | 22   |
| 15° | 202 | 56   |
| 25° | 154 | 71   |
| 35° | 101 | 63   |
| 45° | 47  | 37   |
| 55° | 12  | 13   |
| 65° | 8   | 8    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1286246

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 235.8 |
| 2.5°  | 234.5 |
| 5°    | 231.9 |
| 7.5°  | 226.7 |
| 10°   | 220.2 |
| 12.5° | 212.1 |
| 15°   | 202.0 |
| 17.5° | 191.3 |
| 20°   | 179.3 |
| 22.5° | 166.9 |
| 25°   | 154.3 |
| 27.5° | 141.6 |
| 30°   | 128.9 |
| 32.5° | 115.3 |
| 35°   | 101.3 |
| 37.5° | 87.7  |
| 40°   | 74.7  |
| 42.5° | 60.7  |
| 45°   | 46.8  |
| 47.5° | 35.7  |
| 50°   | 26.0  |
| 52.5° | 16.9  |
| 55°   | 12.0  |
| 57.5° | 10.7  |
| 60°   | 9.7   |
| 62.5° | 8.8   |
| 65°   | 7.8   |
| 67.5° | 6.8   |
| 70°   | 5.8   |
| 72.5° | 4.9   |
| 75°   | 3.9   |
| 77.5° | 3.2   |
| 80°   | 2.6   |
| 82.5° | 1.6   |
| 85°   | 1.0   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)