

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285528

Luminaire Tested: P3AS13R55B2750DE010 E3DLD1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLD1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 640.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285528

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285528

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82		
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74		
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68		
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52		
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48		
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45		
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120341
5°	118798
10°	114115
15°	106743
20°	97378
25°	86860
30°	75986
35°	63122
40°	49779
45°	33740
50°	20639
55°	10705
60°	9955
65°	9391
70°	8719
75°	7710
80°	7577
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33740 cd/sqm

TEST NUMBER: P1285528

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	7.9
10°-20°	131.4	20.5
20°-30°	164.6	25.7
30°-40°	146.9	23.0
40°-50°	86.0	13.4
50°-60°	29.7	4.6
60°-70°	17.9	2.8
70°-80°	10.0	1.6
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.6	54.2
0°-40°	493.5	77.1
0°-60°	609.2	95.2
0°-90°	640.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	640.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	549	
5°	540	51
15°	470	131
25°	359	165
35°	236	147
45°	109	86
55°	28	30
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1285528

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	548.8
2.5°	545.8
5°	539.7
7.5°	527.6
10°	512.5
12.5°	493.6
15°	470.2
17.5°	445.2
20°	417.3
22.5°	388.5
25°	359.0
27.5°	329.6
30°	300.1
32.5°	268.3
35°	235.8
37.5°	204.1
40°	173.9
42.5°	141.4
45°	108.8
47.5°	83.1
50°	60.5
52.5°	39.3
55°	28.0
57.5°	24.9
60°	22.7
62.5°	20.4
65°	18.1
67.5°	15.9
70°	13.6
72.5°	11.3
75°	9.1
77.5°	7.6
80°	6.0
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)