

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285545

Luminaire Tested: P3AS13R55B2750DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 651.0 lumens
Efficiency: N/A
Efficacy: 34.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285545

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285545

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122402
5°	120845
10°	116074
15°	108559
20°	99035
25°	88360
30°	77278
35°	64219
40°	50609
45°	34329
50°	20980
55°	10857
60°	10131
65°	9599
70°	8848
75°	7795
80°	7829
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34329 cd/sqm

TEST NUMBER: P1285545

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	7.9
10°-20°	133.7	20.5
20°-30°	167.4	25.7
30°-40°	149.4	23.0
40°-50°	87.5	13.4
50°-60°	30.2	4.6
60°-70°	18.3	2.8
70°-80°	10.1	1.6
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.5	54.2
0°-40°	501.9	77.1
0°-60°	619.7	95.2
0°-90°	651.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	651.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	549	51
15°	478	134
25°	365	167
35°	240	149
45°	111	87
55°	28	30
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1285545

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	558.2
2.5°	555.1
5°	549.0
7.5°	536.7
10°	521.3
12.5°	502.1
15°	478.2
17.5°	452.9
20°	424.4
22.5°	395.2
25°	365.2
27.5°	335.2
30°	305.2
32.5°	273.0
35°	239.9
37.5°	207.6
40°	176.8
42.5°	143.8
45°	110.7
47.5°	84.6
50°	61.5
52.5°	40.0
55°	28.4
57.5°	25.4
60°	23.1
62.5°	20.8
65°	18.5
67.5°	16.1
70°	13.8
72.5°	11.5
75°	9.2
77.5°	7.7
80°	6.2
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)