

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286305

Luminaire Tested: P3AS02R659030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 35.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286305

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286305

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45567
5°	44948
10°	43442
15°	40954
20°	37780
25°	34308
30°	30384
35°	25859
40°	20581
45°	14513
50°	8426
55°	4588
60°	4298
65°	3891
70°	3526
75°	3304
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14513 cd/sqm

TEST NUMBER: P1286305

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.2	7.5
10°-20°	50.5	19.7
20°-30°	64.9	25.3
30°-40°	60.0	23.4
40°-50°	36.2	14.1
50°-60°	12.3	4.8
60°-70°	7.5	2.9
70°-80°	4.2	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	134.6	52.6
0°-40°	194.6	76.0
0°-60°	243.2	95.0
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	208	
5°	204	19
15°	180	50
25°	142	65
35°	97	60
45°	47	36
55°	12	12
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286305

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	207.8
2.5°	206.8
5°	204.2
7.5°	200.3
10°	195.1
12.5°	188.6
15°	180.4
17.5°	171.7
20°	161.9
22.5°	151.8
25°	141.8
27.5°	131.0
30°	120.0
32.5°	108.9
35°	96.6
37.5°	84.5
40°	71.9
42.5°	59.2
45°	46.8
47.5°	35.4
50°	24.7
52.5°	15.6
55°	12.0
57.5°	10.7
60°	9.8
62.5°	8.5
65°	7.5
67.5°	6.5
70°	5.5
72.5°	4.9
75°	3.9
77.5°	3.3
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)