

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285550

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 274.0 lumens
Efficiency: N/A
Efficacy: 14.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285550

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285550

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74534
5°	72661
10°	67556
15°	60159
20°	51128
25°	41252
30°	31448
35°	22379
40°	14771
45°	8745
50°	5151
55°	3173
60°	2807
65°	2542
70°	2180
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8745 cd/sqm

TEST NUMBER: P1285550

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.7	11.2
10°-20°	73.5	26.8
20°-30°	77.8	28.4
30°-40°	52.6	19.2
40°-50°	23.1	8.4
50°-60°	8.2	3.0
60°-70°	4.8	1.8
70°-80°	2.5	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.9	66.4
0°-40°	234.5	85.6
0°-60°	265.8	97.0
0°-90°	274.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	274.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	340	
5°	330	31
15°	265	73
25°	170	78
35°	84	53
45°	28	23
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1285550

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	339.9
2.5°	337.3
5°	330.1
7.5°	318.5
10°	303.4
12.5°	285.3
15°	265.0
17.5°	242.4
20°	219.1
22.5°	194.6
25°	170.5
27.5°	146.8
30°	124.2
32.5°	102.8
35°	83.6
37.5°	66.3
40°	51.6
42.5°	38.8
45°	28.2
47.5°	20.7
50°	15.1
52.5°	10.5
55°	8.3
57.5°	7.5
60°	6.4
62.5°	5.6
65°	4.9
67.5°	4.1
70°	3.4
72.5°	3.0
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)