

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286310

Luminaire Tested: P3AS02R659030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 325.9 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286310

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1286310

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76880
5°	75963
10°	73078
15°	68445
20°	61559
25°	52285
30°	40892
35°	29152
40°	19064
45°	11784
50°	5970
55°	2103
60°	1842
65°	1868
70°	1667
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11784 cd/sqm

TEST NUMBER: P1286310

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.4	9.9
10°-20°	83.9	25.7
20°-30°	98.1	30.1
30°-40°	68.5	21.0
40°-50°	30.2	9.3
50°-60°	6.7	2.1
60°-70°	3.4	1.0
70°-80°	2.0	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	214.4	65.8
0°-40°	282.9	86.8
0°-60°	319.8	98.1
0°-90°	325.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	325.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	351	
5°	345	32
15°	302	84
25°	216	98
35°	109	69
45°	38	30
55°	6	7
65°	4	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1286310

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	350.6
2.5°	349.3
5°	345.1
7.5°	337.9
10°	328.2
12.5°	316.2
15°	301.5
17.5°	283.7
20°	263.8
22.5°	241.4
25°	216.1
27.5°	189.4
30°	161.5
32.5°	134.5
35°	108.9
37.5°	86.4
40°	66.6
42.5°	50.4
45°	38.0
47.5°	27.9
50°	17.5
52.5°	9.1
55°	5.5
57.5°	4.9
60°	4.2
62.5°	3.9
65°	3.6
67.5°	2.9
70°	2.6
72.5°	2.3
75°	1.9
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)