

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286330

Luminaire Tested: P3AS02R709030D2WDE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709030D2WDE010 E3DLP1H
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 234.0 lumens
Efficiency: N/A
Efficacy: 32.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286330
CATALOG NUMBER: P3AS02R709030D2WDE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1286330
 CATALOG NUMBER: P3AS02R709030D2WDE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	63	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54886
5°	53885
10°	50812
15°	46107
20°	40324
25°	34018
30°	27852
35°	21603
40°	15458
45°	9799
50°	4878
55°	2982
60°	2588
65°	2387
70°	2116
75°	1949
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9799 cd/sqm



TEST NUMBER: P1286330
 CATALOG NUMBER: P3AS02R709030D2WDE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	9.8
10°-20°	56.5	24.1
20°-30°	64.4	27.5
30°-40°	50.3	21.5
40°-50°	24.7	10.6
50°-60°	7.6	3.2
60°-70°	4.5	1.9
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.7	61.4
0°-40°	194.0	82.9
0°-60°	226.4	96.7
0°-90°	234.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	234.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	250	
5°	245	23
15°	203	57
25°	141	64
35°	81	50
45°	32	25
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1286330
CATALOG NUMBER: P3AS02R709030D2WDE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	250.3
2.5°	249.0
5°	244.8
7.5°	237.9
10°	228.2
12.5°	216.8
15°	203.1
17.5°	188.5
20°	172.8
22.5°	156.6
25°	140.6
27.5°	125.0
30°	110.0
32.5°	95.0
35°	80.7
37.5°	67.1
40°	54.0
42.5°	42.0
45°	31.6
47.5°	22.1
50°	14.3
52.5°	9.4
55°	7.8
57.5°	6.8
60°	5.9
62.5°	5.2
65°	4.6
67.5°	3.9
70°	3.3
72.5°	2.6
75°	2.3
77.5°	2.0
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)