

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285566

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.0 lumens
Efficiency: N/A
Efficacy: 31.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285566

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285566

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80	79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162684
5°	158595
10°	147448
15°	131306
20°	111566
25°	90054
30°	68643
35°	48827
40°	32232
45°	19103
50°	11224
55°	6920
60°	6140
65°	5552
70°	4744
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 19103 cd/sqm

TEST NUMBER: P1285566

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	11.2
10°-20°	160.3	26.8
20°-30°	169.8	28.4
30°-40°	114.8	19.2
40°-50°	50.3	8.4
50°-60°	18.0	3.0
60°-70°	10.6	1.8
70°-80°	5.5	0.9
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	397.1	66.4
0°-40°	511.8	85.6
0°-60°	580.1	97.0
0°-90°	598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	720	67
15°	578	160
25°	372	170
35°	182	115
45°	62	50
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1285566

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	741.9
2.5°	736.1
5°	720.5
7.5°	695.0
10°	662.2
12.5°	622.7
15°	578.4
17.5°	529.1
20°	478.1
22.5°	424.7
25°	372.2
27.5°	320.4
30°	271.1
32.5°	224.3
35°	182.4
37.5°	144.6
40°	112.6
42.5°	84.6
45°	61.6
47.5°	45.2
50°	32.9
52.5°	23.0
55°	18.1
57.5°	16.4
60°	14.0
62.5°	12.3
65°	10.7
67.5°	9.0
70°	7.4
72.5°	6.6
75°	4.9
77.5°	4.1
80°	3.3
82.5°	2.5
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)