

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285570

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 838.0 lumens
Efficiency: N/A
Efficacy: 43.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285570

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285570

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230113
5°	227778
10°	219969
15°	203316
20°	175459
25°	138564
30°	98294
35°	63390
40°	38071
45°	21460
50°	11531
55°	4129
60°	3728
65°	3580
70°	3462
75°	3219
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21460 cd/sqm

TEST NUMBER: P1285570

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.3	11.6
10°-20°	247.7	29.6
20°-30°	259.5	31.0
30°-40°	151.4	18.1
40°-50°	56.7	6.8
50°-60°	13.3	1.6
60°-70°	6.9	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.5	72.1
0°-40°	755.9	90.2
0°-60°	825.9	98.6
0°-90°	838.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1049	
5°	1035	97
15°	896	248
25°	573	260
35°	237	151
45°	69	57
55°	11	13
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1285570

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1049.4
2.5°	1046.3
5°	1034.8
7.5°	1016.3
10°	987.9
12.5°	947.9
15°	895.6
17.5°	829.5
20°	751.9
22.5°	665.0
25°	572.7
27.5°	478.2
30°	388.2
32.5°	306.7
35°	236.8
37.5°	179.9
40°	133.0
42.5°	95.3
45°	69.2
47.5°	50.0
50°	33.8
52.5°	19.2
55°	10.8
57.5°	9.2
60°	8.5
62.5°	7.7
65°	6.9
67.5°	6.2
70°	5.4
72.5°	4.6
75°	3.8
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)