

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286348

Luminaire Tested: P3AS05R159030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 254.0 lumens
Efficiency: N/A
Efficacy: 22.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286348
CATALOG NUMBER: P3AS05R159030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1286348
 CATALOG NUMBER: P3AS05R159030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	76	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216978
5°	192604
10°	133754
15°	79092
20°	45061
25°	25743
30°	14255
35°	7602
40°	4208
45°	2264
50°	1433
55°	1109
60°	965
65°	882
70°	769
75°	847
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2264 cd/sqm



TEST NUMBER: P1286348

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	29.3
10°-20°	98.2	38.7
20°-30°	50.6	19.9
30°-40°	19.0	7.5
40°-50°	6.2	2.4
50°-60°	2.7	1.0
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.2	87.9
0°-40°	242.2	95.3
0°-60°	251.0	98.8
0°-90°	254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	990	
5°	875	74
15°	348	98
25°	106	51
35°	28	19
45°	7	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1286348
CATALOG NUMBER: P3AS05R159030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	989.5
1°	987.6
2°	974.6
3°	949.9
4°	917.3
5°	875.0
6°	827.0
7°	774.4
8°	716.0
9°	658.2
10°	600.7
12.5°	462.2
15°	348.4
17.5°	260.8
20°	193.1
22.5°	144.1
25°	106.4
27.5°	77.6
30°	56.3
32.5°	39.9
35°	28.4
37.5°	20.3
40°	14.7
42.5°	10.5
45°	7.3
47.5°	5.4
50°	4.2
52.5°	3.4
55°	2.9
57.5°	2.4
60°	2.2
62.5°	2.0
65°	1.7
67.5°	1.5
70°	1.2
72.5°	1.2
75°	1.0
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)