

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286368

Luminaire Tested: P3AS05R159030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030D2WDE010 E3PHLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 233.0 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286368

CATALOG NUMBER: P3AS05R159030D2WDE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286368

CATALOG NUMBER: P3AS05R159030D2WDE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87208
5°	80079
10°	63793
15°	47673
20°	36216
25°	27413
30°	20282
35°	14482
40°	9904
45°	6946
50°	5902
55°	5811
60°	6008
65°	6382
70°	6475
75°	6693
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 8568 cd/sqm

TEST NUMBER: P1286368

CATALOG NUMBER: P3AS05R159030D2WDE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	13.8
10°-20°	58.9	25.3
20°-30°	52.2	22.4
30°-40°	34.2	14.7
40°-50°	18.3	7.8
50°-60°	13.8	5.9
60°-70°	11.9	5.1
70°-80°	8.2	3.5
80°-90°	3.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.3	61.5
0°-40°	177.5	76.2
0°-60°	209.6	89.9
0°-90°	233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	398	
5°	364	32
15°	210	59
25°	113	52
35°	54	34
45°	22	18
55°	15	14
65°	12	12
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P1286368

CATALOG NUMBER: P3AS05R159030D2WDE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	397.7
2.5°	388.3
5°	363.8
7.5°	327.7
10°	286.5
12.5°	246.8
15°	210.0
17.5°	180.4
20°	155.2
22.5°	132.8
25°	113.3
27.5°	96.0
30°	80.1
32.5°	66.4
35°	54.1
37.5°	43.3
40°	34.6
42.5°	27.4
45°	22.4
47.5°	19.5
50°	17.3
52.5°	16.6
55°	15.2
57.5°	14.4
60°	13.7
62.5°	13.0
65°	12.3
67.5°	10.8
70°	10.1
72.5°	8.7
75°	7.9
77.5°	6.5
80°	5.8
82.5°	5.1
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)