

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285573

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 550.0 lumens
Efficiency: N/A
Efficacy: 28.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285573

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285573

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149615
5°	145872
10°	135602
15°	120750
20°	102629
25°	82819
30°	63124
35°	44892
40°	29627
45°	17583
50°	10302
55°	6346
60°	5614
65°	5085
70°	4360
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 17583 cd/sqm

TEST NUMBER: P1285573

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.5	11.2
10°-20°	147.5	26.8
20°-30°	156.2	28.4
30°-40°	105.5	19.2
40°-50°	46.3	8.4
50°-60°	16.6	3.0
60°-70°	9.7	1.8
70°-80°	5.1	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.2	66.4
0°-40°	470.7	85.6
0°-60°	533.5	97.0
0°-90°	550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	550.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	682	
5°	663	62
15°	532	147
25°	342	156
35°	168	106
45°	57	46
55°	17	17
65°	10	10
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1285573

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	682.3
2.5°	677.0
5°	662.7
7.5°	639.2
10°	609.0
12.5°	572.7
15°	531.9
17.5°	486.6
20°	439.8
22.5°	390.6
25°	342.3
27.5°	294.7
30°	249.3
32.5°	206.3
35°	167.7
37.5°	133.0
40°	103.5
42.5°	77.8
45°	56.7
47.5°	41.6
50°	30.2
52.5°	21.2
55°	16.6
57.5°	15.1
60°	12.8
62.5°	11.3
65°	9.8
67.5°	8.3
70°	6.8
72.5°	6.0
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)