

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285579

Luminaire Tested: P3AS13R60B2750DE010 E3CB1MB\_3500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60B2750DE010 E3CB1MB\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 80CRI , E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1003.0 lumens  
Efficiency: N/A  
Efficacy: 52.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285579

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MB\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285579

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MB\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  |  | 90  | 87  | 84  |  | 88  |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 79  |
| 6   | 88  | 79  | 73  | 69  | 87  | 79  | 73  | 69  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 239520 |
| 5°  | 230002 |
| 10° | 236825 |
| 15° | 239865 |
| 20° | 211792 |
| 25° | 178486 |
| 30° | 144756 |
| 35° | 94281  |
| 40° | 43310  |
| 45° | 16591  |
| 50° | 5561   |
| 55° | 1491   |
| 60° | 1360   |
| 65° | 1193   |
| 70° | 1026   |
| 75° | 1356   |
| 80° | 1010   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16591 cd/sqm

TEST NUMBER: P1285579

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MB\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 100.6  | 10.0      |
| 10°-20°   | 289.3  | 28.8      |
| 20°-30°   | 337.5  | 33.6      |
| 30°-40°   | 217.8  | 21.7      |
| 40°-50°   | 48.8   | 4.9       |
| 50°-60°   | 4.9    | 0.5       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 1.4    | 0.1       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 727.4  | 72.5      |
| 0°-40°    | 945.2  | 94.2      |
| 0°-60°    | 998.8  | 99.6      |
| 0°-90°    | 1003.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1003.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1092 |      |
| 5°  | 1045 | 101  |
| 15° | 1057 | 289  |
| 25° | 738  | 337  |
| 35° | 352  | 218  |
| 45° | 54   | 49   |
| 55° | 4    | 5    |
| 65° | 2    | 2    |
| 75° | 2    | 1    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1285579

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MB\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1092.3 |
| 2.5°  | 1074.4 |
| 5°    | 1044.9 |
| 7.5°  | 1043.4 |
| 10°   | 1063.6 |
| 12.5° | 1076.7 |
| 15°   | 1056.6 |
| 17.5° | 996.1  |
| 20°   | 907.6  |
| 22.5° | 815.3  |
| 25°   | 737.7  |
| 27.5° | 661.7  |
| 30°   | 571.7  |
| 32.5° | 466.2  |
| 35°   | 352.2  |
| 37.5° | 240.5  |
| 40°   | 151.3  |
| 42.5° | 90.8   |
| 45°   | 53.5   |
| 47.5° | 31.0   |
| 50°   | 16.3   |
| 52.5° | 5.4    |
| 55°   | 3.9    |
| 57.5° | 3.1    |
| 60°   | 3.1    |
| 62.5° | 2.3    |
| 65°   | 2.3    |
| 67.5° | 2.3    |
| 70°   | 1.6    |
| 72.5° | 1.6    |
| 75°   | 1.6    |
| 77.5° | 0.8    |
| 80°   | 0.8    |
| 82.5° | 0.8    |
| 85°   | 0.8    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)