

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285590

Luminaire Tested: P3AS13R60B2750DE010 E3CB1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60B2750DE010 E3CB1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 80CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 995.0 lumens
Efficiency: N/A
Efficacy: 52.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285590

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285590

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74	70	68	66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63	62
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67	62	59	58
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237591
5°	228175
10°	234932
15°	237936
20°	210112
25°	177083
30°	143617
35°	93532
40°	42966
45°	16467
50°	5526
55°	1453
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16467 cd/sqm

TEST NUMBER: P1285590

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	10.0
10°-20°	287.0	28.8
20°-30°	334.8	33.6
30°-40°	216.0	21.7
40°-50°	48.4	4.9
50°-60°	4.8	0.5
60°-70°	2.3	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.6	72.5
0°-40°	937.6	94.2
0°-60°	990.9	99.6
0°-90°	995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	995.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1037	100
15°	1048	287
25°	732	335
35°	349	216
45°	53	48
55°	4	5
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1285590

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1083.5
2.5°	1065.8
5°	1036.6
7.5°	1035.1
10°	1055.1
12.5°	1068.2
15°	1048.1
17.5°	988.1
20°	900.4
22.5°	808.8
25°	731.9
27.5°	656.4
30°	567.2
32.5°	462.5
35°	349.4
37.5°	238.6
40°	150.1
42.5°	90.0
45°	53.1
47.5°	30.8
50°	16.2
52.5°	5.4
55°	3.8
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	2.3
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)