

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285591

Luminaire Tested: P3AS13R60B2750DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60B2750DE010 E3CB1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 80CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1062.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285591

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285591

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	253598
5°	243539
10°	250741
15°	253963
20°	224253
25°	188987
30°	153289
35°	99822
40°	45857
45°	17583
50°	5868
55°	1567
60°	1447
65°	1297
70°	1026
75°	1356
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17583 cd/sqm

TEST NUMBER: P1285591

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.5	10.0
10°-20°	306.4	28.8
20°-30°	357.3	33.6
30°-40°	230.6	21.7
40°-50°	51.7	4.9
50°-60°	5.1	0.5
60°-70°	2.5	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	770.2	72.5
0°-40°	1000.8	94.2
0°-60°	1057.6	99.6
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1156	
5°	1106	106
15°	1119	306
25°	781	357
35°	373	231
45°	57	52
55°	4	5
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1285591

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1156.5
2.5°	1137.6
5°	1106.4
7.5°	1104.8
10°	1126.1
12.5°	1140.1
15°	1118.7
17.5°	1054.7
20°	961.0
22.5°	863.3
25°	781.1
27.5°	700.6
30°	605.4
32.5°	493.7
35°	372.9
37.5°	254.6
40°	160.2
42.5°	96.1
45°	56.7
47.5°	32.9
50°	17.2
52.5°	5.7
55°	4.1
57.5°	3.3
60°	3.3
62.5°	2.5
65°	2.5
67.5°	2.5
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)