

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286406

Luminaire Tested: P3AS05R259030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 23.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286406

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286406

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	164219
5°	153202
10°	122732
15°	83315
20°	50404
25°	29469
30°	16787
35°	9235
40°	4895
45°	2574
50°	1501
55°	1109
60°	965
65°	1038
70°	962
75°	847
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2574 cd/sqm

TEST NUMBER: P1286406

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	24.1
10°-20°	100.9	39.4
20°-30°	57.6	22.5
30°-40°	22.8	8.9
40°-50°	7.0	2.7
50°-60°	2.7	1.1
60°-70°	1.9	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.3	86.1
0°-40°	243.1	95.0
0°-60°	252.8	98.7
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	749	
5°	696	62
15°	367	101
25°	122	58
35°	34	23
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286406

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	748.9
1°	747.4
2°	741.3
3°	730.5
4°	715.6
5°	696.0
6°	673.0
7°	647.1
8°	617.0
9°	586.2
10°	551.2
11°	516.7
12°	478.8
13°	441.4
14°	402.9
15°	367.0
17.5°	284.5
20°	216.0
22.5°	162.2
25°	121.8
27.5°	90.3
30°	66.3
32.5°	48.0
35°	34.5
37.5°	24.5
40°	17.1
42.5°	11.7
45°	8.3
47.5°	5.9
50°	4.4
52.5°	3.4
55°	2.9
57.5°	2.7
60°	2.2
62.5°	2.0
65°	2.0
67.5°	1.7
70°	1.5
72.5°	1.2
75°	1.0
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1286406

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)