

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286416

Luminaire Tested: P3AS05R259030D2WDE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286416  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R259030D2WDE010 E3DLD1WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 401.0 lumens  
Efficiency: N/A  
Efficacy: 36.1 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286416  
CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1286416  
 CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	95299
5°	93022
10°	86215
15°	76777
20°	65992
25°	56084
30°	46159
35°	35978
40°	25877
45°	16436
50°	9722
55°	6690
60°	6140
65°	5707
70°	5129
75°	4660
80°	4420
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16436 cd/sqm



TEST NUMBER: P1286416

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.2	9.8
10°-20°	93.9	23.4
20°-30°	106.1	26.5
30°-40°	83.9	20.9
40°-50°	42.4	10.6
50°-60°	17.0	4.2
60°-70°	10.9	2.7
70°-80°	6.0	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.2	59.6
0°-40°	323.1	80.6
0°-60°	382.5	95.4
0°-90°	401.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	401.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	435	
5°	423	39
15°	338	94
25°	232	106
35°	134	84
45°	53	42
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1286416

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	434.6
1°	434.6
2°	433.1
3°	430.6
4°	427.1
5°	422.6
6°	417.1
7°	410.6
8°	403.6
9°	395.7
10°	387.2
11°	377.7
12°	368.7
13°	358.2
14°	348.2
15°	338.2
17.5°	310.2
20°	282.8
22.5°	256.8
25°	231.8
27.5°	207.3
30°	182.3
32.5°	158.9
35°	134.4
37.5°	111.9
40°	90.4
42.5°	70.4
45°	53.0
47.5°	39.5
50°	28.5
52.5°	21.5
55°	17.5
57.5°	16.0
60°	14.0
62.5°	12.5
65°	11.0
67.5°	9.5
70°	8.0
72.5°	7.0
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5



TEST NUMBER: P1286416  
CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)