

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286418

Luminaire Tested: P3AS05R259030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 156.9 lumens
Efficiency: N/A
Efficacy: 14.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286418

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286418

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56991
5°	54677
10°	47895
15°	38502
20°	29589
25°	22380
30°	16180
35°	10734
40°	6527
45°	3783
50°	2422
55°	1950
60°	1710
65°	1505
70°	1282
75°	1271
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3783 cd/sqm

TEST NUMBER: P1286418

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.6	14.4
10°-20°	46.9	29.9
20°-30°	42.4	27.0
30°-40°	25.5	16.2
40°-50°	10.1	6.4
50°-60°	4.7	3.0
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	111.9	71.3
0°-40°	137.4	87.6
0°-60°	152.2	97.0
0°-90°	156.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	156.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	248	23
15°	170	47
25°	92	42
35°	40	25
45°	12	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286418

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	259.9
1°	259.9
2°	258.7
3°	256.0
4°	252.6
5°	248.4
6°	243.1
7°	236.9
8°	229.8
9°	222.7
10°	215.1
11°	206.3
12°	197.3
13°	188.2
14°	179.2
15°	169.6
17.5°	147.1
20°	126.8
22.5°	108.4
25°	92.5
27.5°	77.6
30°	63.9
32.5°	51.4
35°	40.1
37.5°	30.6
40°	22.8
42.5°	16.6
45°	12.2
47.5°	9.3
50°	7.1
52.5°	5.9
55°	5.1
57.5°	4.4
60°	3.9
62.5°	3.2
65°	2.9
67.5°	2.4
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1286418

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)