

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286437

Luminaire Tested: P3AS05R309030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.0 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286437

CATALOG NUMBER: P3AS05R309030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286437

CATALOG NUMBER: P3AS05R309030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	100	97	106	102	99	96	99	97	95		97	95	93		95
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93
5	101	96	92	89	100	95	91	88	93	90	87		92	89	87		90
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		82
10	88	82	78	75	88	81	78	75	81	77	75		80	77	75		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	501254
5°	494716
10°	431923
15°	274531
20°	108766
25°	36341
30°	16914
35°	7656
40°	2948
45°	1427
50°	409
55°	191
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1427 cd/sqm

TEST NUMBER: P1286437

CATALOG NUMBER: P3AS05R309030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.5	32.6
10°-20°	318.7	50.6
20°-30°	82.2	13.0
30°-40°	19.3	3.1
40°-50°	3.8	0.6
50°-60°	0.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.3	96.2
0°-40°	625.6	99.3
0°-60°	629.8	100.0
0°-90°	630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2286	
5°	2248	205
15°	1209	319
25°	150	82
35°	29	19
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1286437

CATALOG NUMBER: P3AS05R309030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2285.9
1°	2284.2
2°	2278.8
3°	2272.7
4°	2263.6
5°	2247.5
6°	2221.3
7°	2177.8
8°	2118.3
9°	2040.8
10°	1939.8
11°	1819.7
12°	1688.7
13°	1537.8
14°	1379.8
15°	1209.3
16°	1042.3
17°	881.4
18°	727.1
19°	585.5
20°	466.1
21°	366.8
22°	288.6
23°	228.4
24°	182.9
25°	150.2
26°	125.2
27°	106.4
28°	92.0
29°	78.7
30°	66.8
32.5°	42.1
35°	28.6
37.5°	17.9
40°	10.3
42.5°	6.8
45°	4.6
47.5°	2.7
50°	1.2
52.5°	0.5
55°	0.5
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2



TEST NUMBER: P1286437

CATALOG NUMBER: P3AS05R309030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)