

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286438

Luminaire Tested: P3AS05R309030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 259.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286438

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90			
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82			
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78			
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75			
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71			
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69			
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151128
5°	143847
10°	120995
15°	87265
20°	54115
25°	30776
30°	17091
35°	9289
40°	4895
45°	2667
50°	1433
55°	918
60°	877
65°	882
70°	769
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Luminance: 2667 cd/sqm

TEST NUMBER: P1286438

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	22.7
10°-20°	104.6	40.4
20°-30°	60.4	23.3
30°-40°	22.9	8.9
40°-50°	7.1	2.7
50°-60°	2.4	0.9
60°-70°	1.6	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.9	86.5
0°-40°	246.8	95.3
0°-60°	256.2	98.9
0°-90°	259.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	689	
5°	654	59
15°	384	105
25°	127	60
35°	35	23
45°	9	7
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286438

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):


0°	
0°	689.2
1°	688.7
2°	684.6
3°	676.8
4°	667.0
5°	653.5
6°	636.4
7°	617.3
8°	596.0
9°	570.6
10°	543.4
11°	514.0
12°	483.0
13°	450.4
14°	417.4
15°	384.4
17.5°	303.1
20°	231.9
22.5°	172.0
25°	127.2
27.5°	92.5
30°	67.5
32.5°	48.7
35°	34.7
37.5°	24.2
40°	17.1
42.5°	12.0
45°	8.6
47.5°	5.9
50°	4.2
52.5°	2.9
55°	2.4
57.5°	2.2
60°	2.0
62.5°	1.7
65°	1.7
67.5°	1.5
70°	1.2
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1286438

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)