

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286442

Luminaire Tested: P3AS05R309030D2WDE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286442  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R309030D2WDE010 E3DL1WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 322.0 lumens  
Efficiency: N/A  
Efficacy: 29.0 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286442  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1286442  
 CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110035
5°	106603
10°	96057
15°	79456
20°	61512
25°	46140
30°	33499
35°	22326
40°	13711
45°	8063
50°	4947
55°	4014
60°	3508
65°	2854
70°	2565
75°	2542
80°	1894
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8063 cd/sqm

TEST NUMBER: P1286442

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.5	13.8
10°-20°	96.4	29.9
20°-30°	87.7	27.2
30°-40°	53.0	16.5
40°-50°	21.3	6.6
50°-60°	9.4	2.9
60°-70°	5.7	1.8
70°-80°	3.1	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	228.6	71.0
0°-40°	281.7	87.5
0°-60°	312.4	97.0
0°-90°	322.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	322.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	502	
5°	484	45
15°	350	96
25°	191	88
35°	83	53
45°	26	21
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286442  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	501.8
1°	501.3
2°	499.3
3°	495.8
4°	490.8
5°	484.3
6°	476.3
7°	467.8
8°	456.9
9°	444.4
10°	431.4
11°	416.4
12°	400.4
13°	384.5
14°	367.0
15°	350.0
17.5°	305.6
20°	263.6
22.5°	224.7
25°	190.7
27.5°	159.8
30°	132.3
32.5°	106.8
35°	83.4
37.5°	63.9
40°	47.9
42.5°	35.0
45°	26.0
47.5°	19.5
50°	14.5
52.5°	11.5
55°	10.5
57.5°	9.0
60°	8.0
62.5°	6.5
65°	5.5
67.5°	5.0
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	1.5
82.5°	1.0
85°	1.0
87.5°	0.5



TEST NUMBER: P1286442  
CATALOG NUMBER: P3AS05R309030D2WDE010 E3DL1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)