

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286450

Luminaire Tested: P3AS05R309030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 157.9 lumens
Efficiency: N/A
Efficacy: 14.2 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286450

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286450

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		68	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53987
5°	52300
10°	47138
15°	38979
20°	30196
25°	22646
30°	16433
35°	10949
40°	6727
45°	3938
50°	2422
55°	1950
60°	1710
65°	1401
70°	1282
75°	1271
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3938 cd/sqm

TEST NUMBER: P1286450

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.9	13.8
10°-20°	47.3	29.9
20°-30°	43.0	27.2
30°-40°	26.0	16.5
40°-50°	10.4	6.6
50°-60°	4.6	2.9
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.2	71.0
0°-40°	138.2	87.5
0°-60°	153.2	97.0
0°-90°	157.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	246	
5°	238	22
15°	172	47
25°	94	43
35°	41	26
45°	13	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286450

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	246.2
1°	246.0
2°	245.0
3°	243.3
4°	240.8
5°	237.6
6°	233.7
7°	229.6
8°	224.2
9°	218.0
10°	211.7
11°	204.3
12°	196.5
13°	188.6
14°	180.1
15°	171.7
17.5°	149.9
20°	129.4
22.5°	110.2
25°	93.6
27.5°	78.4
30°	64.9
32.5°	52.4
35°	40.9
37.5°	31.4
40°	23.5
42.5°	17.1
45°	12.7
47.5°	9.6
50°	7.1
52.5°	5.6
55°	5.1
57.5°	4.4
60°	3.9
62.5°	3.2
65°	2.7
67.5°	2.4
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1286450

CATALOG NUMBER: P3AS05R309030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)