

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285648

Luminaire Tested: P3AS13R60B2750DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60B2750DE010 E3DL1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 796.0 lumens
Efficiency: N/A
Efficacy: 41.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285648

CATALOG NUMBER: P3AS13R60B2750DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285648

CATALOG NUMBER: P3AS13R60B2750DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187967
5°	186176
10°	180758
15°	169354
20°	149883
25°	125378
30°	98268
35°	71286
40°	47432
45°	29553
50°	15999
55°	4626
60°	4298
65°	3943
70°	3911
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29553 cd/sqm

TEST NUMBER: P1285648

CATALOG NUMBER: P3AS13R60B2750DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	10.0
10°-20°	207.0	26.0
20°-30°	235.9	29.6
30°-40°	167.3	21.0
40°-50°	75.9	9.5
50°-60°	16.1	2.0
60°-70°	7.8	1.0
70°-80°	4.8	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.5	65.6
0°-40°	689.8	86.7
0°-60°	781.8	98.2
0°-90°	796.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	796.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	857	
5°	846	80
15°	746	207
25°	518	236
35°	266	167
45°	95	76
55°	12	16
65°	8	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1285648

CATALOG NUMBER: P3AS13R60B2750DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	857.2
2.5°	854.1
5°	845.8
7.5°	831.5
10°	811.8
12.5°	783.8
15°	746.0
17.5°	698.3
20°	642.3
22.5°	581.8
25°	518.2
27.5°	453.2
30°	388.1
32.5°	326.1
35°	266.3
37.5°	213.3
40°	165.7
42.5°	125.6
45°	95.3
47.5°	71.1
50°	46.9
52.5°	21.9
55°	12.1
57.5°	10.6
60°	9.8
62.5°	9.1
65°	7.6
67.5°	6.8
70°	6.1
72.5°	5.3
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)