

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285693

Luminaire Tested: P3AS13R60B2750DE010 E3DLP1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285693  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60B2750DE010 E3DLP1GPH\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 270.0 lumens  
Efficiency: N/A  
Efficacy: 14.1 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285693

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLP1GPH\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285693

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLP1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  | 95  | 94  |  | 92  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 91  | 88  | 86  |  | 85  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 86  | 82  |  | 87  | 84  | 81  |  | 85  | 82  | 79  |  | 78  |
| 4   | 95  | 87  | 81  | 77  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 80  | 76  | 73  |  | 72  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  | 71  | 68  |  | 66  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  | 66  | 63  |  | 62  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 57  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 54  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 60  | 55  | 52  |  | 50  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 56  | 52  | 49  |  | 47  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 68416 |
| 5°  | 66894 |
| 10° | 62635 |
| 15° | 56186 |
| 20° | 48304 |
| 25° | 39946 |
| 30° | 31574 |
| 35° | 23450 |
| 40° | 16145 |
| 45° | 10141 |
| 50° | 5561  |
| 55° | 3250  |
| 60° | 2938  |
| 65° | 2491  |
| 70° | 2116  |
| 75° | 2203  |
| 80° | 1894  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10141 cd/sqm

TEST NUMBER: P1285693

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLP1GPH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 28.3   | 10.5      |
| 10°-20°   | 68.7   | 25.5      |
| 20°-30°   | 75.4   | 27.9      |
| 30°-40°   | 54.9   | 20.3      |
| 40°-50°   | 25.9   | 9.6       |
| 50°-60°   | 8.5    | 3.1       |
| 60°-70°   | 4.8    | 1.8       |
| 70°-80°   | 2.6    | 1.0       |
| 80°-90°   | 0.8    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 172.4  | 63.9      |
| 0°-40°    | 227.3  | 84.2      |
| 0°-60°    | 261.8  | 97.0      |
| 0°-90°    | 270.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 270.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 312 |      |
| 5°  | 304 | 28   |
| 15° | 248 | 69   |
| 25° | 165 | 75   |
| 35° | 88  | 55   |
| 45° | 33  | 26   |
| 55° | 8   | 8    |
| 65° | 5   | 5    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1285693

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLP1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 312.0 |
| 2.5°  | 310.2 |
| 5°    | 303.9 |
| 7.5°  | 294.2 |
| 10°   | 281.3 |
| 12.5° | 265.7 |
| 15°   | 247.5 |
| 17.5° | 227.8 |
| 20°   | 207.0 |
| 22.5° | 185.9 |
| 25°   | 165.1 |
| 27.5° | 144.3 |
| 30°   | 124.7 |
| 32.5° | 105.7 |
| 35°   | 87.6  |
| 37.5° | 71.2  |
| 40°   | 56.4  |
| 42.5° | 43.4  |
| 45°   | 32.7  |
| 47.5° | 23.7  |
| 50°   | 16.3  |
| 52.5° | 10.8  |
| 55°   | 8.5   |
| 57.5° | 7.4   |
| 60°   | 6.7   |
| 62.5° | 5.6   |
| 65°   | 4.8   |
| 67.5° | 4.1   |
| 70°   | 3.3   |
| 72.5° | 3.0   |
| 75°   | 2.6   |
| 77.5° | 1.9   |
| 80°   | 1.5   |
| 82.5° | 1.1   |
| 85°   | 0.7   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)